

Sydney: (02) 9890 9111 Brisbane: (07) 3715 2200 Melbourne: (03) 9212 4422 Perth: (08) 9373 9999

Product Brochure For B419

BAND

21

BLADE

SAW

sales@machineryhouse.com.au www.machineryhouse.com.au

B419 - Metal Band Saw Blade - 4-6TPI Bi-Metal, Blade - 3035 x 27 x 0.90mm

Suitable for Stainless Steel SUITS BS-916 Metal Cutting Band Saw

F

Quality and Consistency

ज्ञातन

Ex GST Inc GST \$88.00 \$80.00 ORDER CODE: B419 Suits Band Saw Models: BS-916 Blade Size (L x W x T) (mm): 3035 x 27 x 0.90 Number of teeth per inch (TPI): 4-6 Blade Type: **BI-METAL** Blade Suitable for - Material Type: Mild & Stainless Steel Suits Section Size (mm): 51-80



Starrett

Description

Please Note:
cb>Starrett Blades are distributed in Sydney & Brisbane
cb>Excision Blades are distributed in Melbourne & Perth

B

IMPORTANT RUN-IN INSTRUCTIONS FOR BI-METAL BLADES

- Avoid excessive feed pressure on run-in
 Run-in at 3/4 normal feed pressure for first 25 square inches on tough material
 After run-in, gradually increase feed to maximum cutting rate



Sydney: (02) 9890 9111 Brisbane: (07) 3715 2200 Melbourne: (03) 9212 4422 Perth: (08) 9373 9999

sales@machineryhouse.com.au www.machineryhouse.com.au

Product Brochure For B419

BLADE SELECTION CHARTS

Band saw tooth size is determined by the size of the cross section to be cut. In general cutting thinner sections requires more teeth per inch, thicker sections require coarser pitches, or less teeth per inch.

To select an appropriate tooth size please refer to the table immediately below unless material to be cut is a tube, in which case refer to the larger table below. For general purpose cutting use a constant pitch blade, for more aggressive production cutting of harder to cut materials use a variable pitch blade.

SOLID SECTION

Section Size (mm)	Constant Pitch (TPI)	Variable Pitch (TPI) 14/18 or 10/14				
Up to 10	24 or 18					
10-15	14	8-12				
16-30	10	6-10 5-8				
31-50	8					
51-80	6	4-6				
81-120	4	3-4				
121-200	3	2-3				
Over 200	2 or 1.25	1.4-2 or 0.8-1.3				



TUBE SECTION

Wall Thickness	Outside diameter of tube or maximum profile section length (mm)												
(mm)	20	40	60	80	100	120	150	200	300	500	600	700	800
2	14	14	14	14	14	14	10-14	10-14	8-12	8-12	6-10	5-8	5-8
3	14	14	10-14	10-14	10-14	10-14	8-12	8-12	6-10	6-10	5-8	5-8	5-8
4	14	14	10-14	10-14	8-12	8-12	6-10	6-10	5-8	5-8	4-6	4-6	4-6
5	14	10-14	10-14	8-12	8-12	6-10	6-10	5-8	5-8	4-6	4-6	4-6	4-6
6	14	10-14	10-14	8-12	8-12	6-10	6-10	5-8	5-8	4-6	4-6	3-4	3-4
8	14	10-14	8-12	8-12	6-10	6-10	5-8	5-8	4-6	4-6	3-4	3-4	3-4
10		8-12	8-12	6-10	6-10	5-8	5-8	4-6	4-6	3-4	3-4	3-4	3-4
12		8-12	6-10	6-10	5-8	5-8	4-6	4-6	3-4	3-4	3-4	3-4	2-3
15			6-10	5-8	5-8	4-6	4-6	4-6	3-4	3-4	3-4	2-3	2-3
20				5-8	4-6	4-6	4-6	3-4	3-4	2-3	2-3	2-3	2-3
30					4-6	4-6	3-4	3-4	3-4	2-3	2-3	2-3	2-3
50						3-4	3-4	3-4	2-3	2-3	2-3	2-3	2-3
75							2-3	2-3	2-3	2-3	2-3	1.4-2	1.4-2